Lutz Drum and Container Pumps

Lightweight, comfortable and powerful

New dimensions of flexibility

With the development of the new battery pumps B1 Battery and B2 Battery, Lutz launches a new dimension of mobility, battery performance, weight, life, capacity and ergonomics and offers maximum flexibility for the user. With the combination possibilities of the pump tubes in PP, PVDF and stainless steel in different lengths, a variety of fluids from different containers can be transferred.

Features/Benefits:

- » BLDC motor with a high level of efficiency up to 70%
- » Infinitely varied
- » Modular construction
- >> Low weight
- » High battery capacity
- » Long service life
- » Low noise < 70 dBA</p>
- » Sophisticated guick-action coupling
- » Available in polypropylene, polyvinylidene fluoride and stainless steel (1.4571)



Mobile pump unit on trolley

For flexible use, the pump and the drum can be easily and quickly brought to any location by the trolley (Order No. 0371-030).

B1 Battery:



Battery life: 25 minutes at max. speed

1 Battery charge = 2 x 200 I Container*

* determined with pump tube PP 25-L SL

B2 Battery:



Battery life: 34 minutes at max. speed

1 Battery charge = 12,6 x 200 | Container*

* determined with pump tube PP 32-R SL

Lutz Drum Pump B1/B2 Battery





Lutz Pump Sets

Pump Set B1/ B2 Battery

Lutz pump sets save time and money. The annoying search for the right pump and accessories has come to an end. Lutz is offering a choice of different pump sets. Optionally, the pumps can be combined with a flow meter. Lutz has optimal solutions for almost all applications.



It's that easy



Replaceable battery with Li-lon technology



BLDC motor






Flow meter TR90



Hose set with nozzle and hose clamps





Suitable pump tube

Lutz Pump Sets

Pump Set B1 Battery (polypropylene)

For thin-bodied fluids

such as battery acid, ammonia water, photographic developer/-fixer, glycols, phosphoric acid, hydrochloric acid and hydrogen peroxide.

For removing small quantities from hobbocks, canisters and drums.

Motor B1 Battery,

70 Watt internally ventilated

Density (kg/dm³)	Viscosity (mPas)	Delivery rate (I/min.)	Delivery head (m wc)
1.3	200	20	6

Max. temperature of medium 50 °C

Specified values are maximum values determined with water at 20°C , measured directly at the pressure joint. Viscosity determined with oil.





For emptying canisters and drums	Set B1 Battery PP 25-L SL			Set B1 Battery PP 25-L SL with flow Meter TR90-PP
Motor B1 Battery	✓			✓
Flow meter TR90-PP	-			✓
Pump tube PP 25-L SL in polypropylene	~			~
1.5 m PVC hose 3/4"	~			✓
Hose clamps	✓			✓
Lutz nozzle	✓			✓
Immersion depths	500 mm	700 mm	1000 mm	1000 mm
Order No.	0207-090	0207-091	0207-092	0207-093
Battery 10.8 V	0332-027			
Battery charger	0335-336			